CGI SYSTEM FOR 1 OXYGEN CYLINDER WITHOUT RACK



DESCRIPTION

All component are carefully selected and according to rules and regulations for the specific condition found on board. This system makes it easy for the user to connect the steel hose outlet nipple to the gas apparatus due to the outlet coil.

The Central Gas Installation System consists of a high pressure hose with safety wire, closing ball valve, CGI regulator, backfire valve, stainless steel outlet coil and outlet connection nipple for welding onto low pressure pipe line.

APPLICATIONS


Pressurize cylinder are heavy and dangerous to move around. By having our Drew Marine Central Gas Installation System, movement of pressurize cylinder are minimize and cylinders can be kept safely in 1 designated location on the upper most continuous deck. Gas is piped to outlet station at location where the gas are needed.

SYSTEM HIGHLIGHTS

- 1 cylinder
- · Established marine standards
- High pressure shut-off valve
- High pressure hoses with safety wire comply to ISO 14113
- Backfire valve comply to ISO 5175

PARAMETERS FOR CGI SYSTEM FOR 1 OXYGEN CYLINDER

Nominal flow:	30 m ³ /h
Max. flow:	40 m ³ /h
Inlet pressure:	max. 200 bar
Outlet pressure:	10 bar




(see enlarged image on back)


TECHNICAL DATA

Gas Purity	up to 4.6	
Pressure Regulator Housing	Brass 2.0402 CuZn40Pb ₂	
Seat Sealing	PA 6.6	
Regulator Diaphragm	EPDM	
High pressure valve	acc. to TPED	
HP hand wheel material	impact resistant MARANYL/Aluminium	
HP valve material	brass 2.0402	
Safety Relief valve	opening pressure 15 - 17 bar	
Working temperature	–30 to 60 °C / -22 to 140 °F	
Pressure gauges	safety version [bar/psi] ISO 5171/EN 562	
High Pressure Hose with Safety Wire	PTFE 200 bar, 600 bar test pressure	
Outlet Coil	welding nipple 12 x 2,5 mm	
Backfire Valve, Acetylene	Safety features: Gas non return valve Pressure sensitive cut off valve Flame arrestor Temperature sensitive cut off valve	






FLOW SCHEME



PERFORMANCE



ORDERING INFORMATION

Part No.	Component	PCN
	CGI System for 1 Oxygen without rack	2205012
1	High Pressure hose with safety wire	0783010
2	Non Return valve	_
3	CGI Closing valve	-
4	CGI Regulator	0741018
5	Content Gauge	0552019
6	Working Gauge	0553017
7	Pressure Relief valve	-
8	Backfire valve	0549024
9	Outlet Coil stainless steel	0520024
10	Outlet Coil connection	9061011
	Plycard CGI Oxygen	9076028
	Plycard Gas Welding safety	9076051
	CGI Pipe clamp	9006017
	CGI Pipe penetration bushing	9008013
	Cylinder Rack assembly for 1 Cyl	9041013
	Cylinder Rack assembly for 2 Cyl	9042011
	Cylinder Rack assembly for 3 Cyl	9043019

Contact your Drew Marine representative for more information



400 Captain Neville Drive Waterbury CT, 06705 USA 1-973-526-5700 Drew-Marine.com

Copyright © Drew Marine. All Rights Reserved. All statements, information and data presented herein are believed to be accurate and reliable but are not to be taken as a guarantee, express warranty or implied warranty of merchantability or fitness for a particular purpose, or representation, express or implied, for which seller assumes legal responsibility, and they are offered solely for your consideration, investigation and verification. Statements or suggestions concerning possible use of this product are made without representation or warranty that any such use is free of patent infringement and are not recommendations to